

Technical datasheet

for Personal Protective Equipment: Universal-Visor Carrier with clip-lock

Artikelno.: GFKHH003-1				Description: Aluminium visor carrier with clip-lock for mounting on industrial helmets with mounting device for safety visors.
EN Norms:				CE-Certificate:
EN 166	EN 167	EN 168	EN 170	C0844UHL/R6
Technical features				
Weight: 135g				
<ul style="list-style-type: none">Visor carrier made of high-quality aluminiumhigh sealing from above, due to a wide overlap of the profiles, when flapped down				<ul style="list-style-type: none">4-level-jointFixation of the safety visor with clip-lockthe visor carrier is fixed on the helmet by a robust steel spring
Used materials:				
Profiles:	Aluminium			
Raster:	Strip steel C75S, hardened and zincd			
Tension spring:	Spring steel X12 Chrome-Nickel 17.7K stainless			
Tube:	Soft-PVC			
Fields of use:				
<ul style="list-style-type: none">Heavy industry: esp. steel industry, foundries, chemical plants				<ul style="list-style-type: none">fire brigade, civil protection
Marking:				
UHL 166 BT CE on front of the T-profile				

Warning!

The safety officer should be contacted to ensure an adequate protection at work.

Plastic can cause an allergic reaction of the skin of sensitive persons.

Eye-protection devices against particles with high velocity could transmit the impact energy, if the device is worn together with standard glasses.

If the eye-protection device is composed of two different devices, only the protection of the device with the lower protection class is given.

Notice relating to the mutual compability of the marking (DIN EN 166 note d, e and f in table 12). If protection against mechanical impacts with high velocity in extreme temperatures is needed, the used eye protection device has to be marked with the letter T after the letter for the impact protection, i.e. BT. Otherwise the eye protection device can only be used against impacts with high velocity in room temperature.

Manufacturer:

RUDOLF UHLEN GmbH

Herstellung von Arbeitsschutzartikeln

Am Höfgen 13 – 42781 Haan

Telephone: +49/2129/1444

Telefax: +49/2129/59980

Internet: www.aschua-uhlen.de

E-Mail: info@aschua-uhlen.de

General manager: Volker Fiedler
Steffen Fiedler

Trade register no.: HRB 17088 Register court Wuppertal

Articlelist

Visor carriers standard

GFKHH001 GFKHH001-1
GFKHH001-3 GFKHH002
GFKHH002-3 GFKHH003
GFKHH003-1 GFKHH003-3
GFKHH003-6 GFKHH003-8
GFKHH004 GFKHH005-2
GFKHH005-4 GFKHH006
GFKHH006-3 GFKHH008
GFKHH008-3 GFKHH009
GFKHH011 GFKHH011-3
GFKHH012 GFKHH012-3
GFKHH015 GFKHH015-3
GFKHH015-3 TATA
GFKTP002

Visor carriers KGS

GFKHH002 KGS
GFKHH002 KGS FLEX
GFKHH003 KGS
GFKHH008 KGS
GFKHH011-3 KGS
GFKHH011-1-3 KGS
GFKHH015 KGS

Face shields PC

GFKVI002 GFKVI002-1
GFKVI002-3 GFKVI002-4
GFKVI002-5 GFKVI002-7
GFKVI002-9 GFKVI016-2
GFKVI016-3 GFKVI045
GFKVI102 GFKVI102-5
GFKVI102-9 GFKVI202
GFKVI202-2 GFKVI204
GFKVI207

Face shields CA

GFKVI007 GFKVI007-4
GFKVI007-7 GFKVI007-9
GFKVI107 GFKVI107-9
GFKVI200 GFKVI200-2

Face shields TA

GFKVI005

Face shields PPSU

GFKVI513


Face shields PC

gold-coated

GFKVI001 GFKVI001-1
GFKVI001-2 GFKVI001-3
GFKVI001-6 GFKVI001-9
GFKVI210 GFKVI210-1
GFKVI210-2 GFKVI210-3
GFKVI210-6 GFKVI210-9

User manual

Aluminium-visor carrier with face shield



1 Helmet
2 Face shield

3 Visor carrier
4 Tension spring



Documentno.:
01.07.2021 / R1

Description

Aluminium-visor carrier

- The visor carrier is the link between the hard hat and the safety visor.
- It is made out of high quality aluminium.
- Due to a powerful tension spring the visor carrier has a secure fit on the hard hat.
- The universal-visor carrier fits all standard hard hats. Different models can be manufactured for special hard hat shapes
- The face shields are attached with a rotating fastener or with a clip fastener.
- The face shields can be lifted into 4 positions.

Face shield

- The face shields are produced in various models. They differ in thickness, shape, shade or material.
- For IR-protection the face shields can be gold-coated.
- On the upper edge the face shields are punched to be attached to the visor carrier.
- The face shields fit both the Rudolf Uhlen visor carriers as well as the Rudolf Uhlen headgear.

Manual

- To attach the visor carrier to the hard hat, the U-profile of the carrier is slid on the brim of the hard hat.
- That followed the tension spring is pulled over the back of the hard hat. Thereby the visor carrier cannot slip off the hard hat.
- Initially the face shield is attached with one of its oval holes on the rotary fastener and fixed by turning the fastener (alternatively it is shoved under the clip fastener).
- That followed the visor is pulled over the visor carrier's positioning pins up to the second rotating fastener / clip fastener. There, it is also fixed by turning the fastener.

Storage

Personal protective equipment should be stored in dry rooms. Especially components made of plastics should not be exposed to intense solar radiation.

Cleaning / Disinfection

The universal-visor carriers and the face-shields can be cleaned with water and standard detergents as well as mild disinfectants. However, the face shields should be dried with compressed air to avoid scratches. Especially the durability of the gold-coated

visors is reduced, when the surface is damaged.

Safety checks

Before using the face shield the user should do a safety check. Damaged or scratched face shields or other damaged parts have to be replaced.

Maintenance / repairs

To be checked on a regular basis:

- Attachment and fit of the visor carrier on the hard hat. Also the tension spring should be checked.
- Folding mechanism of the visor carrier. If necessary the safety nut has to be tightened.
- Attachment of the face shield to the visor carrier. Especially the rotating fasteners have to be checked.
- The face shield has to be checked for its transparency and other damages.

Repairs should only be done with the original parts of the manufacturer.

Decay time / aging

All used materials are exposed to environmental impacts like UV-radiation, acid rain and various other impacts. Therefore especially the personal protective equipment made of thermoplastic plastics should be replaced after 3 years the latest.

Replacement indicators for the visor carriers are mainly the period of use and its overall condition.

Materials used:

Aluminium-visor carrier

- Aluminium profiles
- Tension spring
- Raster made of steel
- PVC-tube
- Rotating fastener or
- Clip fastener

Face shield (varies with the model)

- Polycarbonate 1mm
- Cellulose-Acetate 1,15mm
- Triacetate 1,4mm
- Polyphenylsulfone 2mm
- Iron eyelets
- Gold-coating
- Hard-coating

Marking

Aluminium visor carrier
UHL 166 BT CE

PC-/PPSU-face shield

UHL 1 BT 9 CE

CA-face shield

UHL 1 FT CE

TA-face shield

UHL 1 FT 9 CE

PC-face shield gold-coated

2-5 UHL 1 BT CE
4-4 UHL 1 BT 9 CE 0196
4-5 UHL 1 BT 9 CE 0196
4-6 UHL 1 BT 9 CE 0196

The articles are tested according to
EN 166:2001
EN 170:2002
EN 171:2002

Explanation of the marking:

2-5 = UV-shade
4-4/4-5/= IR-shade
4-6
UHL = Manufacturer: Rudolf Uhlen GmbH
166 = EN standard
1 = optical class
F = mechanical impact with low energy (45 m/s)
B = mechanical impact with medium energy (120 m/s)
T = extr. temperatures
9 = molten metal and hot solids
CE = CE sign
0196 = notified body

DIN CERTCO Gesellschaft für Konformitätsbewertung mbH
Alboinstr. 56
12103 Berlin, Germany
Notified Body: Nr. 0196

General remarks

The face shield should only be used with the correct visor carrier (all Rudolf Uhlen GmbH models). The visor carrier should fit the hard hat properly. In case of doubt users should contact Rudolf Uhlen GmbH.

When approaching the danger zone the face shield has to be flipped down.

The face shields provide protection against mechanical impacts of class „F“ (45m/s) resp. „B“ (120m/s). These

risks were tested under standard conditions.

The user should employ the protective shade according to the work environment. The „Leitfaden für Auswahl und Anwendung“ of DIN EN 171 gives direction for the right choice.

IR-shade	Temp. in °C
4-4	1290
4-5	1390
4-6	1510

For gold-coated face shields of Rudolf Uhlen applies:
The visor is made of polycarbonate. This plastic starts melting at a temperature of 150°C. Although the gold-coating reflects a major part of the radiant heat, this melting temperature will eventually be reached, dependent on the temperature of the heat source as well as the time in front of and the distance to the heat source. At this point at the latest, the operations should be stopped to maintain the full functioning of the face shield.

EU-Baumusterprüfbescheinigung

Inhaber	Rudolf Uhlen GmbH Am Höfgen 13 42781 Haan DEUTSCHLAND
Registernummer	C0844UHL/R6
Produkt	Tragkörper für Gesichtsschutzschilde
Typ, Modell	GFKHH003 / GFKHH004 / GFKHH005 / GFKHH006 / GFKHH008 GFKHH009 / GFKHH011 / GFKHH012 / GFKHH015
Prüfgrundlage(n)	DIN EN 166:2002-04
Prüfberichte/ Prüfzeichen	13721-PZA-17, 13722-PZA-17, 13723-PZA-17, 13724-PZA-17, 13725-PZA-17, 13726-PZA-17, 105217-PZA-19, 105218-PZA-19, 105219-PZA-19, 105220-PZA-19, 105221-PZA-19, 105222-PZA-19, 105223-PZA-19, 105224-PZA-19, 105225-PZA-19, 11751-PZA-21, 10521-PZA-22, 10522-PZA-22, 10523-PZA-22, 10524-PZA-22, 10525-PZA-22, 10526-PZA-22, 10527-PZA-22, 10528-PZA-22, 10529-PZA-22
Kennzeichnung des Produktes	Detaillierte Kennzeichnung siehe Anhang
Gültigkeitszeitraum	2023-06-02 bis 2027-10-08
Konformität	DIN CERTCO bestätigt die Übereinstimmung des Baumusters mit den geltenden grundlegenden Gesundheitsschutz- und Sicherheitsanforderungen nach Anhang II der Verordnung (EU) 2016/425 für persönliche Schutzausrüstung. Die Bewertung beruht auf den vom Hersteller oder vom bevollmächtigten Vertreter eingereichten Prüfmustern, den technischen Unterlagen, sowie dem Prüfbericht des Prüflabors. Eventuell vorhandene Vorgängerversionen dieser EU-Baumusterprüfbescheinigung verlieren hiermit ihre Gültigkeit.

Weitere Informationen siehe Anhang.

2023-06-02

Dipl.-Phys. Carlo Seiser
Benannte Stelle 0196

C. Seiser



ANHANG

Seite 1 von 2

Zertifikat	C0844UHL/R6 von 2023-06-02
Herstellerkennzeichen	UHL
Kennzeichnung des Produktes	UHL 166 BT CE
Produktspezifikationen	<p>Grad der mechanischen Festigkeit: Schutz gegen Teilchen hoher Geschwindigkeit bei extremen Temperaturen BT (120 m/s)</p> <p>Material/Werkstoff: Aluminium, Stahl, PVC Farbe: Silber/schwarz/grau</p>
Weitere Produktinformationen	<p>GFKHH003 Standard GFKHH003-1 (mit Clipbefestigung) GFKHH003-3 (mit Schaumstoffpolsterung) GFKHH003-6 (mit hitzebeständiger Verschraubung) GFKHH003-8 (mit U-Profil aufgebördelt) GFKHH003-3 TATA: Alu-Helmhalterung für Helmtyp BOP mit angenietetem Fensterrahmen 2 x 50 mm und Schaumstoff im U-Profil</p> <p>GFKHH004: Alu-Helmhalterung, Befestigung mit Drehknebel</p> <p>GFKHH005-2: Alu-Helmhalterung für Breitrandhelme (neues U-Profil) GFKHH005-4: Alu-Helmhalterung für Breitrandhelme mit Schaumstoffpolsterung</p> <p>GFKHH006: Alu-Helmhalterung für Helmtyp IRIS (neues U-Profil) GFKHH006- 3: Alu-Helmhalterung mit Schaumstoffpolsterung für Helmtyp IRIS</p> <p>GFKHH008: Alu-Helmhalterung für Helmtyp INTEX/INAP PCG (neues U-Profil) GFKHH008-3: Alu-Helmhalterung mit Schaumstoffpolsterung für Helmtyp INTEX/INAP PCG (neues U-Profil)</p> <p>GFKHH009: Alu-Helmhalterung mit Schaumstoffpolsterung und Pulverbeschichtung für den Bergbau</p> <p>GFKHH011: Alu-Helmhalterung für Helmtyp MSA Thermalgard GFKHH011-3: Alu-Helmhalterung mit Schaumstoffpolsterung für Helmtyp MSA Thermalgard</p>



ANHANG

Seite 2 von 2

Zertifikat

C0844UHL/R6 von 2023-06-02

GFKHH012: Alu-Helmhalterung für Helmtyp Styl 300 (neues U-Profil)
GFKHH012-31: Alu-Helmhalterung mit Schaumstoffpolsterung für Helmtyp Styl 300 (neues U-Profil)

GFKHH015: Alu-Helmhalterung für Helmtyp Centurion/MSA V-Gard (neues U-Profil)
GFKHH015-3: Alu-Helmhalterung mit Schaumstoffpolsterung für Helmtyp Centurion/MSA V-Gard
GFKHH015-3 TATA: Alu-Helmhalterung für Helmtyp Centurion/MSA V-Gard mit angienietetem Fensterrahmen 2 x 50 mm und Schaumstoff im U-Profil

Bestimmungen/Pflichten

Diese EU-Baumusterprüfbescheinigung ist Eigentum von DIN CERTCO und kann zurückgezogen werden, sofern die Bedingungen, die zur ihrer Ausstellung geführt haben, nicht mehr erfüllt sind.

Die Informationsbroschüre (Gebrauchsanweisung) zum genannten Augenschutzprodukt muss in den Amtssprachen des Bestimmungslandes verfasst sein und unter anderem folgende Angaben zur notifizierten Stelle enthalten:

DIN CERTCO Gesellschaft für
Konformitätsbewertung mbH
Alboinstraße 56
12103 BERLIN
DEUTSCHLAND
Kennnummer der notifizierten Stelle: 0196

Auf dem Produkt muss, soweit möglich, eine Typen-, Chargen- oder Seriennummer oder ein anderes Kennzeichen zur Identifikation angebracht sein.

Auf dem Produkt muss, soweit möglich, der Name und die Postanschrift des Herstellers oder, sofern dieser nicht im Europäischen Wirtschaftsraum ansässig ist, der Name und die Postanschrift eines im Europäischen Wirtschaftsraumes ansässigen bevollmächtigten Vertreters oder Einführers angebracht sein.

Auf dem Produkt und dessen Verpackung muss Monat und Jahr der Herstellung und/oder Monat und Jahr des Verfalls unauslöschlich und eindeutig angebracht sein. Es ist nicht gestattet, dass Produkt mit der Kennnummer 0196 zu kennzeichnen.

Jede Änderung am Produkt, den technischen Unterlagen oder dem Qualitätssicherungssystem muss DIN CERTCO schriftlich mitgeteilt werden. Es gelten die Allgemeinen Geschäftsbedingungen von DIN CERTCO.



EU-DECLARATION OF CONFORMITY

1. PPE: **GFKHH003-1**

2. Manufacturer: **Rudolf Uhlen GmbH
Am Höfgen 13
42781 Haan**



3. This declaration of conformity is issued under the sole responsibility of the manufacturer:
Rudolf Uhlen GmbH.

4. Object of the declaration:
Universal visor carrier with Clip-lock

5. The object of the declaration described in point 4 is in conformity with the relevant Union harmonisation legislation: guideline 2001/95/EG and regulation (EU) 2016/425.

6. References to the relevant harmonised standards used, including the date of the standard, or references to the other technical specifications, including the date of the specification, in relation to which conformity is declared: EN 166:2002-04.

7. The notified body DIN CERTCO Gesellschaft für Konformitätsbewertung mbH Alboinstr. 56, 12103 Berlin (0196) performed the EU type-examination (Module B) and issued the EU type-examination certificate **C0844UHL/R6**

8. Additional information:
Signed for and on behalf of:
Rudolf Uhlen GmbH

Haan, 2. June 2023:



Steffen Fiedler
-Geschäftsführer-